

# PRO TIPS: Gaskets

## MATERIAL DOES MATTER

- There are variety of gaskets depending on your application.  
*Call us to find out which gasket is best for your needs.*
  - BUNA: Resists solvents, max temp is 105°C
  - Silicone: Highest temp, max temp is 230°C
  - Viton: Low outgassing, max temp is 150°C

## GET THE MOST OUT OF YOUR GASKET

- Rotate your gasket every few months for longer life
- Remove the gasket from oven ONLY when completely cooled to maintain shape and oven fit
- Only use vacuum oven under vacuum. Using with heat only will build up condensation on the gasket, causing damage

## DON'T BE DOWN

- Keep extra gaskets on hand to limit down time

**Order Extra Gaskets  
@ [cascadesciences.com](https://cascadesciences.com)**